

ELECTRON BEAM MELTED MOLYBDENUM FOR GLASS MELTING ELECTRODES AND MEDICAL TECHNOLOGY

Product Description

Two different molybdenum qualities are produced, normal and premium quality. The material is melted from pure molybdenum by electron beam melting and brought into its final shape by forging and machining.

Applications

The material is used in both the glass industry as a glass melting electrode and the medical technology to produce components for X-ray tubes.

Typical Chemical Composition

Material Molybdenum		Normal Quality (EL)	Premium Quality (LT)
element	dimension		
Mo (balance)	%	min. 99.95	min. 99.97
O	ppm	max. 40	max. 20
C	ppm	max. 30	max. 20
Fe	ppm	max. 40	max. 15
Ni	ppm	max. 15	max. 10
Co	ppm	max. 15	max. 10
Cr	ppm	max. 15	max. 10
Cu	ppm	max. 20	max. 10
Pb	ppm	max. 15	max. 10
Zn	ppm	max. 10	max. 10
Mn	ppm	max. 10	max. 10
W	ppm	max. 300	max. 300
Na	ppm		max. 10
Mg	ppm		max. 10
K	ppm		max. 10
Ca	ppm		max. 20
Cd	ppm		max. 10
Ba	ppm		max. 10
Ti	ppm		max. 10
N	ppm		max. 10
H	ppm		max. 10
S	ppm		max. 20

Microstructure

The material can be offered in forged condition (deformation structure) as well as partially or completely recrystallized (depending on the annealing process). Finished products according to customer drawings or raw products as semi-finished products can be delivered.

Ultrasonic Test

All melted and forged molybdenum rods are inspected by ultrasonic test according to DIN EN 583.

Density

$\rho \geq 10.1 \text{ g/cm}^3$ (both melted and forged)

Dimensions and Tolerances

The material of normal quality can be supplied in the following standard diameters:

32.0 mm (1 ¼")
50.8 mm (2")
63.5 mm (2.5")
76.2 mm (3")
101.6 mm (4")
127.0 mm (5")
152.4 mm (6")

Tolerances: +/- 0.5 mm in lengths up to 2.5 m. Other diameters are possible according to customer request, up to 200 mm are possible.

Please inquire about the dimensions and tolerances for the premium quality.

Straightness

Maximum deviation 1.5 mm / m.

Threads

Male or female threads can be delivered.

Surface quality

Turned; to customer specification ground or blasted.

Identification

Each glass melting electrode and each component is labelled with the batch number and/or consecutive identification number, depending on customer specifications.

STEREON Metals Hermsdorf GmbH
Robert-Friese-Strasse 4
07629 Hermsdorf

Tel.: 036601 922 101
Fax: 036601 922 111
E-Mail: hermsdorf@stereon.com
Internet: www.stereon.com

The conditions of your use and application of our products, technical assistance, and information (whether verbal, written by way of production evaluations), including any suggested formulations and recommendations, are beyond our control. Therefore, it is imperative that you test our products, technical assistance, and information to determine to your own satisfaction whether they are suitable for your intended uses and applications. This application-specific analysis must at least include testing to determine suitability from a technical as well as health, safety, and environmental standpoint. Such testing has not necessarily been done by STEREON. All information is without warranty or guarantee. It formally must be understood and agreed that the customer assumes and hereby expressly releases STEREON from all liability, in tort, contract or otherwise, incurred

Number PD-7103
Issue 6-11.03.2026

in connection with the use of our products, technical assistance and information. Any statement or recommendation not contained herein is unauthorized and shall not bind STEREON. Nothing herein shall be construed as a recommendation to use any product in conflict with patents covering any material or its use. No license is implied or in fact granted under the claims of any patent. In case of order please refer to issue number of this product data sheet. All deliveries are based on the latest issue of the product data sheet and the latest version of our General Conditions of Sale and Delivery.